



Booted Holder

Oseco's Booted Holder is intended for use in corrosive applications

FEATURES

- Available in sizes 1" through 8"
- Excellent for replacing exotic materials such as tantalum
- Non-torque sensitive
- Good for temperatures up to 500° F

Booted Holder

The Oseco fluoropolymer Booted Insert Holder is used in applications where aggressive corrosives are present. A solid PFA insert is pressed into the inner diameter of FRDI and PRDI non-torque-sensitive holders. When used with rupture discs with fluoropolymer liners attached to the process side, only fluoropolymer is in contact with the media.



Insert Holder Dimensional Data for Fluoropolymer-booted FRDI, PRDI

Line Size (inches)	Outer Diameter (inches)		Overall Height (inches)	
	150#	300#	FRDI	PRDI
1	2.5	2.75	1.62	1.75
1.5	3.25	3.62	1.62	1.75
2	4.0	4.25	1.62	1.75
3	5.25	5.75	1.62	1.93
4	6.75	7.0	1.87	2.31
6	8.62	9.75	2.5	2.81
8	10.87	-	2.87	3.43

Please refer to Tables 1 & 2 on the previous page for pressure and temperature limitations.

Oseco Inc
 1701 W. Tacoma
 Broken Arrow Oklahoma 74012 USA
 Tel: (918) 258-5626
 Fax: (918) 251-2809

Visit the products section of oseco.com to ensure you have the most recent information.



www.oseco.com
 Contact Oseco at **800-395-3475**
 or email us at **info@oseco.com**.